

Product specifications

Pam o2 MC is a 3D printer dedicated to the manufacturing of metal and ceramic parts using industrial pellet shape feedstock. It is the most versatile 3D printer enabling to handle the widest variety of materials to create functional prototypes, toolings and small and medium scale series.

- Full setup control
- Most profitable PIM-Like solution
- No volatile powders for no health risks
- Multi-material & Multi-resolution
- Compatible with all PIM post-processing
- Compatible with thermoplastics & TPES

General specifications	3D printing process	Pellet Additive Manufacturing (PAM)
	Number of extruder	Up to 4
	Physical Dimensions	Ø 834 x H 925 mm - 95 kg
	Maximum print volume	Ø300 * H300 mm (no radiant disc). Ø270 * H300 mm (with radiant disc)
	Power	3 500 W
	Power requirements	230 V ~ 8 A - 50Hz - IEC 60320 type C20
Print head	Nozzles sizes	Ø 0.25 - 0.3 - 0.4 - 0.6 - 0.8 - 1.0 - 1.2 - 2.0 - 2.5 mm
	Stepper motor resolution	40µm (Z) and 5µm (X,Y)
	Maximum extrusion temperature	450°C
	Maximum print bed temperature	150°C - 250 °C in option
	Maximum heating room temperature	90°C
	Maximum local radiant disc temperature	300°C
Materials	Grades	Injection molding pellet materials
	Compatible materials	Metal & Ceramic feedstocks, Thermoplastics & TPES
	Maximum viscosity	6 000 Pa.s at negligible shear and process temperature
	Granulometry	Head cutting, cold cutting
	Pellet size	2 - 4 mm
	Supplier	Open
Software	CAD solution	Open (not supplied)
	Slicing	Cura by Pollen AM
	Control software	HoneyPrint SX2
	Network communication	Ethernet protocol

No special facilities needed

You can install a Pam 3D Printer just about anywhere.
No access to gas, air or fluid required.

Pollen AM Headquarter

52 avenue Pierre Semard
FR-94200 Ivry-sur-Seine
France
+33 (0)1 58 46 20 52
contact@pollen.am

